

Δ6 Clear

2.1



	100	3000	4000	5000	6000	8000
Silica	19	570	760	950	1140	1520
EPK Kaolin	20	600	800	1000	1200	1600
Frit 3134	20	600	800	1000	1200	1600
Potash Feldspar (Cluster)	20	600	800	1000	1200	1600
Talc	6	180	240	300	360	480
Wollastonite	15	450	600	750	900	1200
Rutile (optional)	0.5	15	20	25	30	40

Notes:

Add 0.5% Rutile for a stronger glaze
Add 0.5-2% cobalt carbonate for Glossy Blue

Cobalt and iron remain stable.

For best results, keep the application thin. Will be milky if applied too thick.
Original recipe from Mastering Cone 6 Glazes